

Hazardous Location Door Switch



The Hazardous Location Door Switch is designed to be used with nVent HOFFMAN Hazardous Location LED Lights in Class 1, Division 2 hazardous areas. The included hardware kit allows the door switch to easily be mounted and maintain the enclosure rating up to UL Type 4X. This versatile switch activates the LED light when the enclosure door is opened and can be mounted on any flange of the enclosure. The included five-foot connect cable allows ease of wiring to the enclosure back panel.

INDUSTRY STANDARDS

Switch Rating

Explosion-proof for Class 1, Division 2, Groups A, B, C, and D

FEATURES

Class 1, Division 2 hazardous areas

Maintains the enclosure rating up to UL Type 4X

Five foot connection cable

Ease of wiring to the enclosure back panel

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
LEDHLSWITCH	27194	0.39in	0.71in	1.1in	Plastic	Smooth

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE