

## Inner Doors, ADI



Displays and indicators can be mounted on a surface within the enclosure while covering other components, and preventing unauthorized access.

### FEATURES

Description: For controls, meters, lamps, etc. Hinges can be mounted to allow left or right hand opening. Lock double-bit 3 mm insert; 700 mm high doors and above have 2 locks. Usable depth between inner and external door: 35 mm. Adjustable depth position with AMG accessory. Workable area: H-55, W- 108. 19" version available on request. Machining is required for stainless steel enclosures.

Material: Door 1.5 mm mild steel, vertical top and bottom profiles 2 mm mild steel.

Finish: RAL 7035 structured powder coating.

Protection: IP 2XC.

Pack quantity: Inner door, two vertical profiles, top and bottom profiles and mounting accessories.

## SPECIFICATIONS

**Thickness:** 16ga  
**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Door Size	Latch Quantity
ADI04030R5	ADI04030R5	14.72in	10.28in	2.8in	13.58 x 7.56in	1
ADI04040R5	ADI04040R5	14.72in	14.72in	2.8in	13.58 x 11.50in	1
ADI04050R5	ADI04050R5	14.72in	18.15in	2.8in	13.58 x 15.43in	1
ADI04060R5	ADI04060R5	14.72in	22.09in	2.8in	13.58 x 19.37in	1
ADI05030R5	ADI05030R5	18.66in	10.28in	2.8in	17.52 x 7.56in	1
ADI05040R5	ADI05040R5	18.66in	14.72in	2.8in	17.52 x 11.50in	1
ADI05050R5	ADI05050R5	18.66in	18.15in	2.8in	17.52 x 15.43in	1
ADI06040R5	ADI06040R5	22.6in	14.72in	2.8in	21.46 x 11.50in	1
ADI06050R5	ADI06050R5	22.6in	18.15in	2.8in	21.46 x 15.43in	1
ADI06060R5	ADI06060R5	22.6in	22.09in	2.8in	21.46 x 19.37in	1
ADI06080R5	ADI06080R5	22.6in	29.96in	2.8in	21.46 x 27.24in	1
ADI07050R5	ADI07050R5	26.54in	18.15in	2.8in	25.39 x 15.43in	2
ADI08040R5	ADI08040R5	30.47in	14.72in	2.8in	29.33 x 11.50in	2
ADI08060R5	ADI08060R5	30.47in	22.09in	2.8in	29.33 x 19.37in	2
ADI08080R5	ADI08080R5	30.47in	29.96in	2.8in	29.33 x 27.24in	2
ADI10060R5	ADI10060R5	38.35in	22.09in	2.8in	37.20 x 19.37in	2

Catalog Number	Article Number	Height	Width	Depth	Door Size	Latch Quantity
ADI10080R5	ADI10080R5	38.35in	29.96in	2.8in	37.20 x 27.24in	2
ADI12060R5	ADI12060R5	46.22in	22.09in	2.8in	45.08 x 19.37in	2
ADI12080R5	ADI12080R5	46.22in	29.96in	2.8in	45.07 x 27.24in	2

## ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**