


Ladder Rack Curved Sections (cULus Classified)



The Ladder Rack Curved Sections provide a vertical change in direction. They are made of 1-1/2 inch x 3/8 inch (38 mm x 8 mm) tubular steel with a painted or plated finish. Cross members are welded on the inside (inside bends) or outside (outside bends) of the section. They connect to straight section with butt-splice kits. They are also designed for category 5e, 6, 6A and fiber optic cable.

FEATURES

The Ladder Rack Curved Sections provide a vertical change in direction

They are made of 1-1/2 inch x 3/8 inch (38 mm x 8 mm) tubular steel with a painted or plated finish

Cross members are welded on the inside (inside bends) or outside (outside bends) of the section

They connect to straight section with butt-splice kits

They are also designed for category 5e, 6, 6A and fiber optic cable

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
LIB12BLK	10053	Mild Steel	Powder Coated	Jet Black	RAL 9005	16ga
LIB12G	10052	Mild Steel	Powder Coated	Gray	ANSI 61	16ga
LIB12GZ	10054	Mild Steel	Zinc Plated			16ga
LIB12W	29918	Mild Steel	Powder Coated	White		16ga
LIB15BLK	29987	Mild Steel	Powder Coated	Jet Black	RAL 9005	16ga
LIB15W	29988	Mild Steel	Powder Coated	White		16ga
LIB18BLK	10056	Mild Steel	Powder Coated	Jet Black	RAL 9005	16ga
LIB18G	10055	Mild Steel	Powder Coated	Gray	ANSI 61	16ga
LIB18GZ	10057	Mild Steel	Zinc Plated			16ga
LIB18W	29922	Mild Steel	Powder Coated	White		16ga
LIB24BLK	17337	Mild Steel	Powder Coated	Jet Black	RAL 9005	16ga
LIB24W	29924	Mild Steel	Powder Coated	White		16ga
LIB6BLK	10047	Mild Steel	Powder Coated	Jet Black	RAL 9005	16ga
LIB6G	10046	Mild Steel	Powder Coated	Gray	ANSI 61	16ga
LIB6GZ	10048	Mild Steel	Zinc Plated			16ga
LIB6W	29916	Mild Steel	Powder Coated	White		16ga
LOB12BLK	10038	Mild Steel	Powder Coated	Jet Black	RAL 9005	16ga
LOB12G	10037	Mild Steel	Powder Coated	Gray	ANSI 61	16ga
LOB12GZ	10042	Mild Steel	Zinc Plated			16ga

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
LOB12W	29921	Mild Steel	Powder Coated	White		16ga
LOB15BLK	29985	Mild Steel	Powder Coated	Jet Black	RAL 9005	16ga
LOB15W	29986	Mild Steel	Powder Coated	White		16ga
LOB18BLK	10044	Mild Steel	Powder Coated	Jet Black	RAL 9005	16ga
LOB18G	10043	Mild Steel	Powder Coated	Gray	ANSI 61	16ga
LOB18GZ	10045	Mild Steel	Zinc Plated			16ga
LOB18W	29923	Mild Steel	Powder Coated	White		16ga
LOB24BLK	17336	Mild Steel	Powder Coated	Jet Black	RAL 9005	16ga
LOB24W	29925	Mild Steel	Powder Coated	White		16ga
LOB6BLK	10035	Mild Steel	Powder Coated	Jet Black	RAL 9005	16ga
LOB6G	10034	Mild Steel	Powder Coated	Gray	ANSI 61	16ga
LOB6GZ	10036	Mild Steel	Zinc Plated			16ga
LOB6W	29917	Mild Steel	Powder Coated	White		16ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE