


Mounting Profiles 19-Inch , CIP



19" equipment can be easily fitted in floor standing enclosures, either in the factory or in the field, when these profiles are used.

FEATURES

Description: Full height mounting profiles to achieve 482.6 mm (19") mounting requirements on all sides. Fully adjustable in depth.

Material: 2 mm zinc plated steel.

Pack quantity: 1 pair.

Mounting requirements: To be used in conjunction with CIB or CID profiles. For partial height mounting the CIWR is required.

SPECIFICATIONS

Thickness: 14ga
Material: Mild Steel
Finish: Zinc Plated

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth | Rack Units | Enclosure Material |
|----------------|----------------|---------|--------|--------|------------|--------------------|
| CIP20 | CIP20 | 39.37in | 1.77in | 1.14in | 20U | Mild Steel |
| CIP22 | | 43.31in | 1.77in | 1.14in | 22U | Mild Steel |
| CIP24 | CIP24 | 47.24in | 1.77in | 1.14in | 24U | Mild Steel |
| CIP29 | CIP29 | 55.11in | 1.77in | 1.14in | 29U | Mild Steel |
| CIP33 | CIP33 | 63in | 1.77in | 1.14in | 33U | Mild Steel |
| CIP38 | CIP38 | 70.87in | 1.77in | 1.14in | 38U | Mild Steel |
| CIP42 | CIP42 | 78.74in | 1.77in | 1.14in | 42U | Mild Steel |
| CIP47 | CIP47 | 86.61in | 1.77in | 1.14in | 47U | Mild Steel |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE