

Mounting Rail, CP



This mounting rail can be cut to size and is ideal when components are fixed with sliding nuts.

FEATURES

Description: Installation profile with and without 25 mm hole pattern. Add GLM sliding nuts for easy installation of components.

Material: Galvanized steel.

Pack quantity: 10 x 2 m.

SPECIFICATIONS

Thickness: 0.06in
Finish: Galvanized
Material: Mild Steel

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Holes Included	Quick Ship
CP1020H	CP1020H	0.39in	0.79in	78.74in	Yes	No
CP1020U	CP1020U	0.39in	0.79in	78.74in	No	No
CP2020H	CP2020H	0.79in	0.79in	78.74in	Yes	No
CP2020U	CP2020U	0.79in	0.79in	78.74in	No	No
CP2040H	CP2040H	0.79in	1.57in	78.74in	Yes	No
CP2040U	CP2040U	0.79in	1.57in	78.74in	No	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE