

Panels for Junction Box



Use these panels in Junction Boxes. Available in various materials to meet various application requirements. Stainless steel and aluminum panels are protected on one side with a plastic film.

FEATURES

Panel mounting hardware is furnished with all enclosures which accept these panels

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Material	Finish	Color
A10P8AL	55650	8.75in	6.75in	Aluminum	Anodized	
A10P10AL	17381	6.75in	6.88in	Aluminum	Anodized	
A12P10AL	55660	10.75in	8.75in	Aluminum	Anodized	
A14P12AL	55670	12.75in	10.75in	Aluminum	Anodized	
A16P14AL	55680	14.75in	12.88in	Aluminum	Anodized	
A18P16AL	58500	16.75in	14.88in	Aluminum	Anodized	
A20P16JAL	32876	18.75in	14.88in	Aluminum	Anodized	
A6P4AL	55620	4.88in	2.88in	Aluminum	Anodized	
A6P6AL	55630	4.88in	4.88in	Aluminum	Anodized	
A8P6AL	55640	6.75in	4.88in	Aluminum	Anodized	
A8P8AL	17378	8.75in	8.88in	Aluminum	Anodized	
A4P4G	21494	2.88in	2.88in	Mild Steel	Galvanized	
A6P4	54750	4.88in	2.88in	Mild Steel	Powder Coated	White
A6P4G	26049	4.88in	2.88in	Mild Steel	Galvanized	
A6P4SS	55550	4.88in	2.88in	Stainless Steel 304	Brushed #3	
A6P6SS	55560	4.88in	4.88in	Stainless Steel 304	Brushed #3	
A6P6	54760	4.88in	4.88in	Mild Steel	Powder Coated	White
A6P6G	26059	4.88in	4.88in	Mild Steel	Galvanized	
A8P6	54770	6.75in	4.88in	Mild Steel	Powder Coated	White

Catalog Number	Article Number	Height	Width	Material	Finish	Color
A8P6SS	55570	6.75in	4.88in	Stainless Steel 304	Brushed #3	
A9P6G	21495	7.38in	4.63in	Mild Steel	Galvanized	
A7P7G	23796	5.88in	5.88in	Mild Steel	Galvanized	
A8P6G	26069	6.75in	4.88in	Mild Steel	Galvanized	
A8P8	54820	6.75in	6.88in	Mild Steel	Powder Coated	White
A8P8G	17447	6.75in	6.88in	Mild Steel	Galvanized	
A12P6	54950	10.75in	4.88in	Mild Steel	Powder Coated	White
A12P6G	15142	10.75in	4.88in	Mild Steel	Galvanized	
A10P8	54780	8.75in	6.88in	Mild Steel	Powder Coated	White
A10P8SS	55580	8.75in	6.75in	Stainless Steel 304	Brushed #3	
A10P8G	26079	8.75in	6.88in	Mild Steel	Galvanized	
A10P10	54830	8.75in	8.88in	Mild Steel	Powder Coated	White
A10P10G	15141	8.75in	8.88in	Mild Steel	Galvanized	
A12P10	54790	10.75in	8.88in	Mild Steel	Powder Coated	White
A14P8	54000	12.75in	6.88in	Mild Steel	Powder Coated	White
A14P8G	15143	12.75in	6.88in	Mild Steel	Galvanized	
A12P10G	26089	10.75in	8.88in	Mild Steel	Galvanized	
A12P10SS	55590	10.75in	8.75in	Stainless Steel 304	Brushed #3	
A12P12G	15312	10.75in	10.88in	Mild Steel	Galvanized	

Catalog Number	Article Number	Height	Width	Material	Finish	Color
A12P12	54840	10.75in	10.88in	Mild Steel	Powder Coated	White
A12P12SS	55490	10.75in	10.75in	Stainless Steel 304	Brushed #3	
A14P12	54800	12.75in	10.88in	Mild Steel	Powder Coated	White
A14P12G	26099	12.75in	10.88in	Mild Steel	Galvanized	
A14P12SS	55600	12.75in	10.75in	Stainless Steel 304	Brushed #3	
A16P10	54270	14.75in	8.88in	Mild Steel	Powder Coated	White
A16P10G	15145	14.75in	8.88in	Mild Steel	Galvanized	
A16P14	54810	14.75in	12.88in	Mild Steel	Powder Coated	White
A16P14G	26109	14.75in	12.88in	Mild Steel	Galvanized	
A16P14SS	55610	14.75in	12.88in	Stainless Steel 304	Brushed #3	
A18P16	58480	16.75in	14.88in	Mild Steel	Powder Coated	White
A18P16G	26119	16.75in	14.88in	Mild Steel	Galvanized	
A18P16SS	58490	16.75in	14.88in	Stainless Steel 304	Brushed #3	
A20P16J	32875	18.75in	14.88in	Mild Steel	Powder Coated	White

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE