

Panels for Junction Box and Wall-Mount Enclosure Plastic



Manufactured from reinforced phenolic laminate sheet stock. This material has exceptional strength and chemical resistance, which makes it ideally suited for the most corrosive environments. Composite panels may be drilled and tapped but work equally as well with self-threading or thread-cutting screws. Refer to the table for recommended mounting specifications.

FEATURES

Intended for use in corrosion-resistant enclosures

SPECIFICATIONS

Color: Light Brown
Material: Phenolic
Finish: Smooth Matte

Table 1/1

Catalog Number	Article Number	Height	Width	Thickness	Hole Diameter	Quick Ship
A6P4C	65570	4.88in	2.88in	0.12in	0.25in	No
A10P8C	65600	8.75in	6.88in	0.12in	0.25in	No
A12P10C	65610	10.75in	8.88in	0.12in	0.25in	No
A14P12C	65620	12.75in	10.88in	0.12in	0.25in	No
A16P14C	65630	14.75in	12.88in	0.12in	0.25in	No
A18P16C	58510	16.75in	14.88in	0.12in	0.25in	No
A20P16C	65640	17in	13in	0.12in		No
A20P20C	65650	17in	17in	0.12in		No
A24P20C	65660	21in	17in	0.12in		No
A24P24C	65670	21in	21in	0.12in		No
A30P24C	65680	27in	21in	0.12in		No
A6P6C	65580	4.88in	4.88in	0.12in	0.25in	No
A8P6C	65590	6.75in	4.88in	0.12in	0.25in	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE