

Pedestal with Legs



Pedestal with legs is used to support various HMI enclosures and provides optimal viewing and operating height. Four sturdy, die-cast legs bolt to the one-piece mild steel vertical tube for rigidity. Legs will accept casters in limited applications. Heavy-duty black polymer caps fit on ends of legs to cover bolts or levelers. Two heights are available as standard offering to meet your ergonomic requirements.

FEATURES

Use 4.00 x 4.00-in. (102 x 102-mm) pedestal with Concept HMI and InLine HMI Enclosures

Use 8.00 x 8.00-in. (203 x 203-mm) pedestal with ProLine Sloped-Front HMI Enclosures

Attach pedestal to HMI base with cutout, swivel, swivel tilt or angle adapter with pre-drilled holes

Hardware and gasket to attach enclosure are included

SPECIFICATIONS

Thickness: 14ga
Finish: Powder Coated

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Color
AP26L44	37710	26in	4in	4in	Mild Steel	Gray
AP26L44LG	13244	26in	4in	4in	Mild Steel	Light Gray
AP26L88	37690	26in	8in	8in	Mild Steel	Gray
AP26L88LG	42419	26in	8in	8in	Mild Steel	Light Gray
AP36L44	37700	36in	4in	4in	Mild Steel	Gray
AP36L44LG	13243	36in	4in	4in	Mild Steel	Light Gray
AP36L88	37680	36in	8in	8in	Mild Steel	Gray
AP36L88LG	42409	36in	8in	8in	Mild Steel	Light Gray

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE