

ProLine 100-mm Plinth Base



Plinth Bases install under an enclosure to provide space for cables to enter from below. A Plinth Base consists of four corner supports connected to four access panels. The corner supports are cast aluminum. The access panels attach to the corner supports with screws. All necessary mounting hardware included. Order a gland plate system to provide Type 12 protection when using a Plinth Base.

FEATURES

All necessary mounting hardware included

Order with a gland plate system to provide Type 12 protection when using a Plinth Base

SPECIFICATIONS

Thickness: 16ga
Color: Jet Black
Finish: Powder Coated
Color Code: RAL 9005

Table 1/1

Catalog Number	Article Number	Material	Quick Ship
PPB166	97370	Mild Steel	No
PPB168	97380	Mild Steel	No
PPB185	97430	Mild Steel	No
PPB188	97450	Mild Steel	No
PPB164	97350	Mild Steel	No
PPB186	97440	Mild Steel	No
PPB1105	97470	Mild Steel	No
PPB1106	97480	Mild Steel	No
PPB1108	97490	Mild Steel	No
PPB184	97420	Mild Steel	No
PPB145	25579	Mild Steel	No
PPB146	25589	Mild Steel	No
PPB165	97360	Mild Steel	No
PPB176	97390	Mild Steel	No
PPB178	97400	Mild Steel	No
PPB189	97460	Mild Steel	No

Catalog Number	Article Number	Material	Quick Ship
PPB179	97410	Mild Steel	No
PPB1124	23419	Mild Steel	No
PPB1125	23429	Mild Steel	No
PPB1126	23439	Mild Steel	No
PPB1128	23449	Mild Steel	No
PPB1165	23459	Mild Steel	No
PPB1166	23469	Mild Steel	No
PPB1168	23479	Mild Steel	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE