

ProLine 100mm Solid Base Cable Entry Gland Plate



Fits all standard ProLine 100-mm Solid Base gland openings. Solid Base gland openings. Can be used in place of standard solid gland plates furnished with 100-mm Solid Base. Adjustable opening for cable entry is foam-lined to maintain a dust-tight seal.

INDUSTRY STANDARDS

UL Listed; Type 1

This component is rated UL Type 1. Installing this component on an enclosure brings the enclosure rating to UL Type 1.

FEATURES

Fits all standard ProLine 100-mm Solid Base gland openings

Foam-lined cable entry ensures a dust-tight seal

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Material	Color	Color Code	Finish	Thickness
PCEGP	22469	Mild Steel	Jet Black	RAL 9005	Powder Coated	14ga

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE