

## ProLine 200-mm Plinth Base



Plinth Bases install under an enclosure to provide space for cables to enter from below. A Plinth Base consists of eight corner supports connected to four access panels. The corner supports are cast aluminum. The access panels attach to the corner supports with screws. Plinth Bases include all necessary mounting hardware. Order a gland plate system to provide Type 12 protection when using a plinth base.

### FEATURES

---

Consists of eight corner supports connected to four access panels

Order a gland plate system to provide Type 12 protection

Includes all mounting hardware

## SPECIFICATIONS

**Thickness:** 16ga  
**Color:** Jet Black  
**Finish:** Powder Coated  
**Color Code:** RAL 9005

Table 1/1

Catalog Number	Article Number	Material	Quick Ship
PPB266	97520	Mild Steel	No
PPB268	97530	Mild Steel	No
PPB285	97580	Mild Steel	No
PPB288	97600	Mild Steel	No
PPB286	97590	Mild Steel	No
PPB2105	97620	Mild Steel	No
PPB2106	97630	Mild Steel	No
PPB2108	97640	Mild Steel	No
PPB284	97570	Mild Steel	No
PPB245	25619	Mild Steel	No
PPB276	97540	Mild Steel	No
PPB289	97610	Mild Steel	No
PPB2124	23489	Mild Steel	No
PPB2125	23499	Mild Steel	No
PPB2126	23509	Mild Steel	No
PPB2128	23519	Mild Steel	No

Catalog Number	Article Number	Material	Quick Ship
PPB2165	23529	Mild Steel	No
PPB2166	23539	Mild Steel	No
PPB2168	23549	Mild Steel	No

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE