

ProLine Disconnect Doors



Disconnect Doors provide a means to mount flange-mount disconnects to ProLine Enclosures. Hinged mullion provides unobstructed access to interior, thus easing equipment installation.

Disconnect mullion is hinged to provide easy disconnect installation and maximum access to subpanel. Removable door bar is included on disconnect door. A flush handle with defeater operates an internal 3-point latch system on disconnect door and latches to the disconnect mullion. Interlocking is provided from Primary door to disconnect mullion. The disconnect mullion and disconnect door include 140-degree hinges and are gasketed to maintain enclosure integrity.

FEATURES

Includes a flush handle with defeater and 3-point latching system

Enclosures with a preferred cutout will accept the disconnect switches listed in the Preferred Cutout Overview section.

Enclosures with a large cutout will accept the disconnect switches listed in the Large Cutout Overview section.

SPECIFICATIONS

Thickness: 14ga
Color: Light Gray
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Material	Dimensions	Cutout Type	Quick Ship
PLTDDC166	35639	Mild Steel	60.59 x 23.39in	Preferred left-hand	No
PTDDC166	35629	Mild Steel	60.59 x 23.39in	Preferred right-hand	No
PLTDDC168	22939	Mild Steel	60.59 x 31.26in	Preferred left-hand	No
PTDDC168	36570	Mild Steel	60.59 x 31.26in	Preferred right-hand	No
PLTDDC1810	22969	Mild Steel	68.46 x 39.13in	Preferred left-hand	No
PTDDC1810	36940	Mild Steel	68.46 x 39.13in	Preferred right-hand	No
PTDDC186	35649	Mild Steel	68.46 x 23.39in	Preferred right-hand	No
PLTDDC188	22949	Mild Steel	68.46 x 31.26in	Preferred left-hand	No
PTDDC188	36580	Mild Steel	68.46 x 31.26in	Preferred right-hand	No
PTDLDC2010	22679	Mild Steel	76.34 x 39.13in	Large right-hand	No
PTDDC2010	36950	Mild Steel	76.34 x 39.13in	Preferred right-hand	No
PLTDDC2010	22979	Mild Steel	76.34 x 39.13in	Preferred left-hand	No
PTDLDC206	35709	Mild Steel	76.34 x 23.39in	Large right-hand	No
PTDDC206	35669	Mild Steel	76.34 x 23.39in	Preferred right-hand	No
PLTDDC208	22959	Mild Steel	76.34 x 31.26in	Preferred left-hand	No
PTDDC208	36590	Mild Steel	76.34 x 31.26in	Preferred right-hand	No

ADDITIONAL PRODUCT DETAILS

Allen-Bradley: Large handle to be used with 400A or greater disconnect switches and 600A or greater circuit breakers.

Siemens ITE: MAX-FLEX™ FHOHN handle used with MD 800 amp, ND (1200 amp), PD (1600 amp) and RD (2000 amp).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE