

ProLine FloTek PC Passive Cooling Server Cabinet



Designed deeper to house servers and manage power cables, ProLine FloTek Cabinets rely on optimized passive airflow for cooling. The cabinets may be placed in data rooms randomly or in hot/cold aisle configurations.

INDUSTRY STANDARDS

UL Listed to UL 508A File Number E61997

cUL Listed to CSA C22.2 No. 14-18

EIA 310-D (RU – Rack Unit spacing, marking, and positioning)

IEC 60529, IP20

Perforated doors meet or exceed manufactures open space/air flow ventilation requirements

FEATURES

Fully perforated front and rear doors and fully perforated top allow maximum air movement around equipment; conforms to server manufacturer open space requirements

Rigid front door made of aluminum extrusions and formed perforated steel offers highly attractive appearance and durability

Models without sides fit together quickly for easy installation in ganged applications

Three-point locking pushbutton swing handle on front door provides easy but controlled access; two keys included

Rear doors are split for easy access and include 3-point, low-profile, locking swing handle

Two sets of 19-inch square-hole rack angles support both front and rear of equipment

Rack angles are infinitely adjustable from front to rear for positioning flexibility

Large gland plate in top allows easy routing of cable, pre-terminated cables and patch panels

Open bottom with integral bolt-down brackets

SPECIFICATIONS

Color: Jet Black
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 9005

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Thickness	Rack Units
PSCPC20610B	15604	78.37in	23.94in	39.34in	16ga	42U
PSCPC20610BNS	15608	78.37in	23.58in	39.34in	16ga	42U
PSCPC20611B	15605	78.37in	23.94in	43.28in	16ga	42U
PSCPC20611BNS	15611	78.37in	23.58in	43.28in	16ga	42U
PSCPC20612B	15606	78.37in	23.94in	47.22in	16ga	42U
PSCPC20612BNS	15612	78.37in	23.58in	47.22in	16ga	42U
PSCPC2069B	15603	78.37in	23.94in	35.4in	16ga	42U
PSCPC2069BNS	15607	78.37in	23.58in	35.4in	16ga	42U
PSCPC21610B	26377	85.08in	23.87in	39.33in	16ga	45U
PSCPC21611B	26378	85.08in	23.87in	43.27in	16ga	45U
PSCPC21612B	26381	85.08in	23.87in	47.2in	16ga	45U
PSCPC2169B	26376	85.08in	23.87in	35.39in	16ga	45U
PSCPC24610B	26383	94.92in	23.87in	39.33in	16ga	51U
PSCPC24611B	26384	94.92in	23.87in	43.27in	16ga	51U
PSCPC24612B	26385	94.92in	23.87in	47.2in	16ga	51U

Catalog Number	Article Number	Height	Width	Depth	Thickness	Rack Units
PSCPC2469B	26382	94.92in	23.87in	35.39in	16ga	51U

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE