

# ProLine G2 Fully Sealed Plinth (100mm Solid Base)



No need to use a gland plate in the base of the enclosure with the Fully-Sealed Plinth Base (100mm Solid Base), which includes fully-sealed gland plates on the sides. Solid bases can easily be joined, for convenient cable management in joined/ganged enclosures while maintaining Type 12 environmental rating.

## FEATURES

Maintains NEMA 12 rating without requiring gland plate

Two side gland plates for cable management options

Seamless polyurethane gasket (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Optional Cable Entry Gland Plate for additional cable management solutions

Welded corners

Drill points for locating casters (not included)

Installation hardware included

## SPECIFICATIONS

**Color:** Jet Black  
**Finish:** Powder Coated  
**Color Code:** RAL 9005

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Material	Thickness
P2B145	30936	3.94in	18.3in	15.7in	Mild Steel	16ga
P2B146	30937	3.94in	22.2in	15.7in	Mild Steel	16ga
P2B164	30938	3.94in	14.4in	23.6in	Mild Steel	16ga
P2B165	30941	3.94in	18.3in	23.6in	Mild Steel	16ga
P2B166	30943	3.94in	22.2in	23.6in	Mild Steel	16ga
P2B166HF	30942	3.94in	22.2in	23.6in	Mild Steel	16ga
P2B168	30944	3.94in	30.1in	23.6in	Mild Steel	16ga
P2B1104	30912	3.94in	14.4in	39.3in	Mild Steel	14ga
P2B1105	30913	3.94in	18.3in	39.3in	Mild Steel	14ga
P2B1106	30915	3.94in	22.2in	39.3in	Mild Steel	14ga
P2B1106HF	30914	3.94in	22.2in	39.3in	Mild Steel	14ga
P2B1108	30916	3.94in	30.1in	39.9in	Mild Steel	14ga
P2B1124	30917	3.94in	14.4in	47.2in	Mild Steel	14ga
P2B1125	30918	3.94in	18.3in	47.2in	Mild Steel	14ga
P2B1126	30921	3.94in	22.2in	47.2in	Mild Steel	14ga
P2B1128	30922	3.94in	30.1in	47.2in	Mild Steel	14ga
P2B1164	30923	3.94in	14.4in	63in	Mild Steel	14ga

Catalog Number	Article Number	Height	Width	Depth	Material	Thickness
P2B1165	30924	3.94in	18.3in	63in	Mild Steel	14ga
P2B1166	30925	3.94in	22.2in	63in	Mild Steel	14ga
P2B1168	30926	3.94in	30.1in	63in	Mild Steel	14ga
P2B1184	34068	3.94in	14.4in	70.8in	Mild Steel	14ga
P2B1185	30927	3.94in	18.3in	70.8in	Mild Steel	14ga
P2B1186	30928	3.94in	22.2in	70.8in	Mild Steel	14ga
P2B1188	30931	3.94in	30.1in	70.8in	Mild Steel	14ga
P2B1810	30945	3.94in	38in	31.5in	Mild Steel	14ga
P2B184	30946	3.94in	14.4in	31.5in	Mild Steel	14ga
P2B185	30947	3.94in	18.3in	31.5in	Mild Steel	14ga
P2B186	30951	3.94in	22.2in	31.5in	Mild Steel	14ga
P2B186HF	30948	3.94in	22.2in	31.5in	Mild Steel	14ga
P2B188	30952	3.94in	30.1in	31.5in	Mild Steel	14ga

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**