

# ProLine G2 Plinth Base



ProLine G2 Plinth Bases install under an enclosure to provide space for cables to enter from below.

## FEATURES

---

Four access panels for cable management options at the base of the enclosure

Sturdy cast aluminum corner supports for superior performance under load

Corner blocks can be installed onto the base of the frame independent of the cover plates, enabling the cover plates to be attached after integration and just prior to shipment

Stackable up to 400mm in height using Plinth Base Stacking Kit (not included)

100 mm or 200 mm options

To maintain a NEMA Type 12 environmental rating, gland plate must also be used in the base of the enclosure

Installation hardware included

## SPECIFICATIONS

**Thickness:** 16ga  
**Color:** Jet Black  
**Finish:** Powder Coated  
**Color Code:** RAL 9005

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Material	Quick Ship
P2BP1104	31066	3.94in	39.33in	14.33in	Mild Steel	No
P2BP1105	31067	3.94in	39.33in	18.27in	Mild Steel	No
P2BP1106	31071	3.94in	39.33in	22.21in	Mild Steel	No
P2BP1108	31072	3.94in	39.33in	30.08in	Mild Steel	No
P2BP1124	31073	3.94in	47.21in	14.33in	Mild Steel	No
P2BP1125	31074	3.94in	47.21in	18.27in	Mild Steel	No
P2BP1126	31075	3.94in	47.21in	22.21in	Mild Steel	Yes
P2BP1128	31076	3.94in	47.21in	30.07in	Mild Steel	No
P2BP1164	31077	3.94in	62.95in	14.33in	Mild Steel	No
P2BP1165	31078	3.94in	62.95in	18.27in	Mild Steel	Yes
P2BP1166	31081	3.94in	62.95in	22.21in	Mild Steel	Yes
P2BP1168	31082	3.94in	62.95in	30.07in	Mild Steel	No
P2BP1184	34072	3.94in	70.83in	14.33in	Mild Steel	No
P2BP1185	31083	3.94in	70.83in	18.27in	Mild Steel	No
P2BP1186	31084	3.94in	70.83in	22.21in	Mild Steel	Yes
P2BP1188	31085	3.94in	70.83in	30.07in	Mild Steel	No

Catalog Number	Article Number	Height	Width	Depth	Material	Quick Ship
P2BP145	31086	3.94in	15.71in	18.27in	Mild Steel	No
P2BP146	31087	3.94in	15.71in	22.21in	Mild Steel	No
P2BP164	31088	3.94in	23.58in	14.33in	Mild Steel	No
P2BP165	31091	3.94in	23.58in	18.27in	Mild Steel	No
P2BP166	31093	3.94in	23.58in	22.21in	Mild Steel	No
P2BP168	31094	3.94in	23.58in	30.08in	Mild Steel	No
P2BP1810	31095	3.94in	31.46in	37.95in	Mild Steel	No
P2BP184	31096	3.94in	31.46in	14.33in	Mild Steel	No
P2BP185	31097	3.94in	31.46in	18.27in	Mild Steel	No
P2BP186	31101	3.94in	31.46in	22.21in	Mild Steel	No
P2BP188	31102	3.94in	31.46in	30.08in	Mild Steel	Yes
P2BP2104	31112	7.58in	39.33in	14.33in	Mild Steel	No
P2BP2105	31113	7.58in	39.33in	18.27in	Mild Steel	No
P2BP2106	31115	7.58in	39.33in	22.21in	Mild Steel	No
P2BP2108	31116	7.58in	39.33in	30.07in	Mild Steel	No
P2BP2124	31117	7.58in	47.21in	14.33in	Mild Steel	No
P2BP2125	31118	7.58in	47.21in	18.27in	Mild Steel	No
P2BP2126	31121	7.58in	47.21in	22.21in	Mild Steel	No
P2BP2128	31122	7.58in	47.21in	31.08in	Mild Steel	No
P2BP2164	31123	7.58in	62.95in	14.33in	Mild Steel	No

Catalog Number	Article Number	Height	Width	Depth	Material	Quick Ship
P2BP2165	31124	7.58in	62.95in	18.27in	Mild Steel	No
P2BP2166	31125	7.58in	62.95in	22.21in	Mild Steel	No
P2BP2168	31126	7.58in	62.95in	31.08in	Mild Steel	No
P2BP2184	34067	7.58in	70.83in	14.33in	Mild Steel	No
P2BP2185	31127	7.58in	70.83in	18.27in	Mild Steel	No
P2BP2186	31128	7.58in	70.83in	22.21in	Mild Steel	No
P2BP2188	31131	7.58in	70.83in	31.08in	Mild Steel	No
P2BP245	31132	7.58in	15.71in	18.27in	Mild Steel	No
P2BP246	31133	7.58in	15.71in	22.21in	Mild Steel	No
P2BP264	31134	7.58in	23.58in	14.33in	Mild Steel	No
P2BP265	31135	7.58in	23.58in	18.27in	Mild Steel	No
P2BP266	31137	7.58in	23.58in	22.21in	Mild Steel	No
P2BP268	31138	7.58in	23.58in	30.07in	Mild Steel	No
P2BP2810	31141	7.58in	39.33in	37.95in	Mild Steel	No
P2BP284	31142	7.58in	31.46in	14.33in	Mild Steel	No
P2BP285	31143	7.58in	31.46in	18.27in	Mild Steel	No
P2BP286	31145	7.58in	31.46in	22.21in	Mild Steel	Yes
P2BP288	31146	7.58in	31.46in	30.07in	Mild Steel	No

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**