

ProLine G2 Solid Doors (Single or Overlapping Double)



ProLine G2 Solid Doors (Single or Overlapping Double) feature a solid swing and a high load capacity. The Smooth Glide latching system is made from quality components and incorporates an innovative timed latch action ensuring a solid door seal with a low closure force. Sold individually.

FEATURES

Smooth Glide latching system – for a smooth, reliable and repeatable door close over enclosure lifetime

Low-profile Swing Handle with key lock; other options available

Seamless polyurethane gasket (UL Component Recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Single doors available for frames up to 1000 mm wide

Overlapping double doors available for frames 800 mm wide and greater

Door bar system on all doors

Timed latch engagement to ensure top and bottom of door catch reliably

Durable, double-flanged latch rod and three Delrin® rollers to prevent metal-on-metal grinding

3-point latch system for doors ≥ 1000 mm in height

Key lock handle standard; other options available

Single doors can be hinged on left or right (default left); overlapping double doors can have the primary door as the left or right door (default right)

Solid Doors are finished with paint over plated surfaces

140-degree hinging standard (180-degree hinge option available)

Door can be reversed without removing the side covers

Can be used on front or rear of enclosure; can be used on the sides of enclosure with side door adapter (not included)

Two grounding studs

All mounting hardware included

Sold individually

Overlapping Double Doors – Additional Specifications: Primary door with Smooth Glide latching system; Secondary door has two latch points with a center lever to ensure secure door closure

SPECIFICATIONS

Thickness: 14ga
Color: Light Gray
Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Material	Door Quantity
P2D105	32982	38.7in	19.6in	0.79in	Mild Steel	
P2D106	31358	38.7in	23.5in	0.79in	Mild Steel	
P2D108	31361	38.7in	31.4in	0.79in	Mild Steel	
P2D125	33683	46.6in	19.6in	0.79in	Mild Steel	
P2D126	31362	46.6in	23.5in	0.79in	Mild Steel	
P2D128	31363	46.6in	31.4in	0.79in	Mild Steel	
P2D145	32983	54.4in	19.6in	0.79in	Mild Steel	
P2D146	31365	54.4in	23.5in	0.79in	Mild Steel	
P2D146HF	31364	54.4in	23.5in	0.79in	Mild Steel	1
P2D164	33684	62.3in	15.7in	0.79in	Mild Steel	
P2D165	32984	62.3in	19.6in	0.79in	Mild Steel	
P2D166	31367	62.3in	23.5in	0.79in	Mild Steel	
P2D168	31368	62.3in	31.4in	0.79in	Mild Steel	
P2D1810	31372	70.2in	39.3in	0.79in	Mild Steel	
P2D184	31373	70.2in	15.7in	0.79in	Mild Steel	
P2D185	32985	70.2in	19.6in	0.79in	Mild Steel	

Catalog Number	Article Number	Height	Width	Depth	Material	Door Quantity
P2D186	31374	70.2in	23.5in	0.79in	Mild Steel	
P2D186HF	32928	70.2in	23.5in	0.79in	Mild Steel	1
P2D187	33641	70.2in	27.5in	0.79in	Mild Steel	
P2D188	31375	70.2in	31.4in	0.79in	Mild Steel	
P2D189	32988	70.2in	35.4in	0.79in	Mild Steel	
P2D2010	31376	78.1in	39.3in	0.79in	Mild Steel	
P2D205	32986	78.1in	19.6in	0.79in	Mild Steel	
P2D206	31381	78.1in	23.5in	0.79in	Mild Steel	
P2D206HF	31378	78.1in	23.5in	0.79in	Mild Steel	1
P2D207	33642	78.1in	27.5in	0.79in	Mild Steel	
P2D208	31383	78.1in	31.4in	0.79in	Mild Steel	
P2D208HF	31382	78.1in	31.4in	0.79in	Mild Steel	1
P2D2210	31384	85.9in	39.3in	0.79in	Mild Steel	
P2D225	32987	85.9in	19.6in	0.79in	Mild Steel	
P2D226	31385	85.9in	23.5in	0.79in	Mild Steel	
P2D226HF	32932	85.9in	23.5in	0.79in	Mild Steel	1
P2D227	33643	85.9in	27.5in	0.79in	Mild Steel	
P2D228	31386	85.9in	31.4in	0.79in	Mild Steel	
P2D228HF	32933	85.9in	31.4in	0.79in	Mild Steel	1
P2D64	31387	23in	15.7in	0.79in	Mild Steel	

Catalog Number	Article Number	Height	Width	Depth	Material	Door Quantity
P2D66	31388	23in	23.5in	0.79in	Mild Steel	
P2D68	31391	23in	31.4in	0.79in	Mild Steel	
P2D86	31392	30.8in	23.5in	0.79in	Mild Steel	
P2D88	31393	30.8in	31.4in	0.79in	Mild Steel	
P2D01012	31517	38.7in	47.2in	0.79in	Mild Steel	
P2D0108	31518	38.7in	31.4in	0.79in	Mild Steel	
P2D01212	31521	46.6in	47.2in	0.79in	Mild Steel	
P2D0128	31522	46.6in	31.4in	0.79in	Mild Steel	
P2D01412	31523	54.4in	47.2in	0.79in	Mild Steel	
P2D0148	31524	54.4in	31.4in	0.79in	Mild Steel	
P2D01612	31525	62.3in	47.2in	0.79in	Mild Steel	
P2D01616	31526	62.3in	62.9in	0.79in	Mild Steel	
P2D0168	31527	62.3in	31.4in	0.79in	Mild Steel	
P2D01810	31531	70.2in	39.3in	0.79in	Mild Steel	
P2D01810HF	31528	70.2in	39.3in	0.79in	Mild Steel	2
P2D01816	31533	70.2in	62.9in	0.79in	Mild Steel	
P2D01818	31534	70.2in	70.8in	0.79in	Mild Steel	
P2D0188	31535	70.2in	31.4in	0.79in	Mild Steel	
P2D02012	31537	78.1in	47.2in	0.79in	Mild Steel	
P2D02016	31538	78.1in	62.9in	0.79in	Mild Steel	

Catalog Number	Article Number	Height	Width	Depth	Material	Door Quantity
P2D02018	31541	78.1in	70.8in	0.79in	Mild Steel	
P2D0208	31543	78.1in	31.4in	0.79in	Mild Steel	
P2D0208HF	31542	78.1in	31.4in	0.79in	Mild Steel	2
P2D02212	31545	85.9in	47.2in	0.79in	Mild Steel	
P2D02216	31546	85.9in	62.9in	0.79in	Mild Steel	
P2D02218	31547	85.9in	70.8in	0.79in	Mild Steel	
P2D0228	31548	85.9in	31.4in	0.79in	Mild Steel	
P2D0228HF	32934	85.9in	31.4in	0.79in	Mild Steel	2
P2D068	31551	23in	31.4in	0.79in	Mild Steel	
P2D088	31552	30.8in	31.4in	0.79in	Mild Steel	
P2D1810HF	31371				Mild Steel	1
P2D148	31366				Mild Steel	
P2D204	31377				Mild Steel	
P2D209	32992				Mild Steel	
P2D229	32993				Mild Steel	
P2D01812	31532				Mild Steel	
P2D02010	31536				Mild Steel	
P2D02210	31544				Mild Steel	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE