

ProLine G2 Transportation Base



ProLine G2 Transportation Bases provide enhanced stability and forklift provisions for modular enclosures up to a maximum of 3000 mm (118.11) total width in a multiple-bay system.

FEATURES

Removable side cover plates allows wire access between bases

Can be used across bayed enclosures up to a maximum of 300mm (118.11in.) total width

Maintains NEMA 12 rating without requiring gland plate

Gasket and installation hardware included

Unique design allows forklift access from each end

Can be configured in a variety of combinations

SPECIFICATIONS

Thickness: 10ga
Color: Jet Black
Finish: Powder Coated
Color Code: RAL 9005

Table 1/1			
Catalog Number	Article Number	Material	Quick Ship
P2BT104	31156	Mild Steel	No
P2BT105	31157	Mild Steel	No
P2BT106	31158	Mild Steel	No
P2BT108	31161	Mild Steel	No
P2BT124	31162	Mild Steel	No
P2BT125	31163	Mild Steel	No
P2BT126	31164	Mild Steel	No
P2BT128	31165	Mild Steel	No
P2BT164	31166	Mild Steel	No
P2BT165	31167	Mild Steel	No
P2BT166	31168	Mild Steel	No
P2BT168	31171	Mild Steel	No
P2BT185	31172	Mild Steel	No
P2BT186	31173	Mild Steel	No
P2BT188	31174	Mild Steel	No
P2BT45	31175	Mild Steel	No

Catalog Number	Article Number	Material	Quick Ship
P2BT46	31176	Mild Steel	No
P2BT64	31177	Mild Steel	No
P2BT65	31178	Mild Steel	No
P2BT66	31181	Mild Steel	No
P2BT68	31182	Mild Steel	No
P2BT810	31183	Mild Steel	No
P2BT84	31184	Mild Steel	No
P2BT85	31185	Mild Steel	No
P2BT86	31186	Mild Steel	No
P2BT88	31187	Mild Steel	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE