

# ProLine G2 Vented Plinth Base Cover



The Vented Plinth Base Covers replace the traditional solid plinth base covers that mount width-wise across the front and rear of the enclosure. Vented covers allow air to enter the enclosure from below, and are used in conjunction with the Vented Gland Plate.

## FEATURES

---

Mounting hardware included

## SPECIFICATIONS

**Thickness:** 16ga  
**Color:** Jet Black  
**Finish:** Powder Coated  
**Color Code:** RAL 9005

Table 1/1

| Catalog Number | Article Number | Frame Type | Material   | Quick Ship |
|----------------|----------------|------------|------------|------------|
| P2APBVC8       | 36148          | Single-Bay | Mild Steel | No         |
| P2APBVC18      | 36154          | Double-Bay | Mild Steel | No         |
| P2APBVC16      | 36153          | Double-Bay | Mild Steel | No         |
| P2APBVC6       | 36147          | Single-Bay | Mild Steel | No         |
| P2APBVC12      | 36152          | Double-Bay | Mild Steel | No         |
| P2APBVC10      | 36151          | Single-Bay | Mild Steel | No         |

## ADDITIONAL PRODUCT DETAILS

Please note that a standard 100mm Solid Plinth Base must be ordered separately, as Vented Plinth Base Covers are replacements for the front and rear covers only. Vented Gland Plate also sold separately, but required for successful air passage.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**