

ProLine G2 Window Doors



ProLine G2 Window Doors can be used to enable viewing of electronic equipment. Featuring clean, contemporary lines, they are available in clear safety glass or polycarbonate and include a standard door bar system for easy accessory attachment. The Smooth Glide latching system is made from high-quality components and features an innovative timed latch action which ensures a solid door seal with a low closure force.

FEATURES

Safety glass or polycarbonate (for food and beverage applications)

Smooth Glide latching system – for a smooth, reliable and repeatable door close over enclosure lifetime

Clean, contemporary design

Window doors available for frames up to 1000 mm wide

0.25 in. (6.35 mm) thick window to provide maximum protection and viewing area

Standard door bar system on all window doors for easy accessories attachment

Low-profile Swing Handle with key lock; other options available

Seamless polyurethane gasket (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Timed latch engagement to ensure top and bottom of door catch reliably

Durable, double-flanged latch rod and three Delrin® rollers to prevent metal-on-metal grinding

3-point latch system for doors ≥ 1000 mm in height

Doors can be hinged on left or right (default left)

14-degree hinging standard (180-degree hinge option available)

Door can be reversed without removing the side covers

Can be used on front or rear of the ProLine G2 frame; can be used on the sides with side door adapter (not included)

Two grounding studs

All mounting hardware included

SPECIFICATIONS

Thickness: 14ga
Color: Light Gray
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Material	Door Quantity	Quick Ship
P2DWG68	31654	Mild Steel		No
P2DW106	31554	Mild Steel		No
P2DW108	31555	Mild Steel		No
P2DW126	31557	Mild Steel		No
P2DW128	31558	Mild Steel		No
P2DW146	31563	Mild Steel		No
P2DW148	31564	Mild Steel		No
P2DW166	31567	Mild Steel		No
P2DW168	31568	Mild Steel		No
P2DW1810	31572	Mild Steel		No
P2DW184	31576	Mild Steel		No
P2DW186	31577	Mild Steel		No
P2DW188	31578	Mild Steel		No
P2DW2010	31581	Mild Steel		No
P2DW204	31585	Mild Steel		No
P2DW206	31587	Mild Steel		No

Catalog Number	Article Number	Material	Door Quantity	Quick Ship
P2DW208	31591	Mild Steel		No
P2DW2210	31592	Mild Steel		No
P2DW226	31596	Mild Steel		No
P2DW228	31597	Mild Steel		No
P2DW64	31598	Mild Steel		No
P2DW66	31601	Mild Steel		No
P2DW68	31602	Mild Steel		No
P2DW86	31603	Mild Steel		No
P2DW88	31604	Mild Steel		No
P2DWG106	31606	Mild Steel		No
P2DWG108	31607	Mild Steel		No
P2DWG126	31611	Mild Steel		No
P2DWG128	31612	Mild Steel		No
P2DWG146	31615	Mild Steel		No
P2DWG148	31616	Mild Steel		No
P2DWG166	31621	Mild Steel		No
P2DWG168	31622	Mild Steel		No
P2DWG1810	31624	Mild Steel		No
P2DWG184	31628	Mild Steel		No
P2DWG186	31631	Mild Steel		No

Catalog Number	Article Number	Material	Door Quantity	Quick Ship
P2DWG188	31632	Mild Steel		No
P2DWG2010	31633	Mild Steel		No
P2DWG204	31637	Mild Steel		No
P2DWG206	31641	Mild Steel		No
P2DWG208	31643	Mild Steel		No
P2DWG2210	31644	Mild Steel		No
P2DWG226	31648	Mild Steel		No
P2DWG228	31651	Mild Steel		No
P2DWG64	31652	Mild Steel		No
P2DWG66	31653	Mild Steel		No
P2DWG86	31655	Mild Steel		No
P2DWG88	31656	Mild Steel		No
P2DW01012	31553	Mild Steel	2	No
P2DW01212	31556	Mild Steel	2	No
P2DW01412	31561	Mild Steel	2	No
P2DW01612	31565	Mild Steel	2	No
P2DW01616	31566	Mild Steel	2	No
P2DW01812	31573	Mild Steel	2	No
P2DW01816	31574	Mild Steel	2	No
P2DW01818	31575	Mild Steel	2	No

Catalog Number	Article Number	Material	Door Quantity	Quick Ship
P2DW02012	31582	Mild Steel	2	No
P2DW02016	31583	Mild Steel	2	No
P2DW02018	31584	Mild Steel	2	No
P2DW02212	31593	Mild Steel	2	No
P2DW02216	31594	Mild Steel	2	No
P2DW02218	31595	Mild Steel	2	No
P2DWOG1012	31605	Mild Steel	2	No
P2DWOG1212	31608	Mild Steel	2	No
P2DWOG1412	31613	Mild Steel	2	No
P2DWOG1612	31617	Mild Steel	2	No
P2DWOG1616	31618	Mild Steel	2	No
P2DWOG1812	31625	Mild Steel	2	No
P2DWOG1816	31626	Mild Steel	2	No
P2DWOG1818	31627	Mild Steel	2	No
P2DWOG2012	31634	Mild Steel	2	No
P2DWOG2016	31635	Mild Steel	2	No
P2DWOG2018	31636	Mild Steel	2	No
P2DWOG2212	31645	Mild Steel	2	No
P2DWOG2216	31646	Mild Steel	2	No
P2DWOG2218	31647	Mild Steel	2	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE