

ProLine Gland Plate



Adjustable Gland Plates are used to seal the bottom of the ProLine frame. Solid, vented and shielded Gland Plates are available. Solid and filtered gland plates include covers that are gasketed to maintain Type 12 enclosure requirements. All installation hardware is included. Solid Gland Plate and EMC Gland Plate are accessories to 100-mm Solid Base, 100-mm/200-mm Plinth Base, Mobile Base and Transportation Base. These gland plates can be used without a base if casters, levelers or frame feet are installed. EMC Gland Plate maintains a Type 1 rating.

FEATURES

Solid Gland Plate and EMC Gland Plate are accessories to 100-mm Solid Base, 100-mm/200-mm Plinth Base, Mobile Base and Transportation Base. These gland plates can be used without a base if casters, levelers or frame feet are installed.

Solid Gland Plate: the Solid Gland Plate can be used with all ProLine subpanels or rack angles. The gland plate consists of a base mounting surface and two adjustable foam-gasketed plates that permit cable entry. The plate can be rotated 180 degrees for front or rear cable entry.

EMC Gland Plate: This gland plate can be used with subpanels or rack angles. Gland plate consists of a base mounting surface and two adjustable gland plates (both have a conductive coating) with conductive fabric-over-foam gasket for cable entry.

Filtered (Vented) Gland Plate: Filtered Gland Plate is used only in conjunction with Vented Plinth Base Covers. The plate can be used with all ProLine subpanels or rack angles. It consists of a mounting base, three adjustable plates for cable entry, a filter and filter retaining rails. Manufactured from 16 gauge steel and finished with RAL 7035 textured light-gray polyester powder paint. Replacement filters available. EMC Gland Plate maintains a Type 1 rating.

All hardware included

SPECIFICATIONS

Thickness: 14ga
Color: Light Gray
Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Material	Finish	Quick Ship
PGP66	29789	Mild Steel	Powder Coated	No
PGPV66	14684	Mild Steel	Powder Coated	No
PGPV68	14685	Mild Steel	Powder Coated	No
PGP68	29799	Mild Steel	Powder Coated	No
PGPV85	14691	Mild Steel	Powder Coated	No
PGP85	29849	Mild Steel	Powder Coated	No
PGPV88	14693	Mild Steel	Powder Coated	No
PGP88	29869	Mild Steel	Powder Coated	No
PGPV64	14682	Mild Steel	Powder Coated	No
PGP64	29769	Mild Steel	Powder Coated	No
PGPV86	14692	Mild Steel	Powder Coated	No
PGP86	29859	Mild Steel	Powder Coated	No
PGP105	29889	Mild Steel	Powder Coated	No
PGPV106	14696	Mild Steel	Powder Coated	No
PGP106	29899	Mild Steel	Powder Coated	No
PGPV108	14697	Mild Steel	Powder Coated	No
PGP108	29909	Mild Steel	Powder Coated	No

Catalog Number	Article Number	Material	Finish	Quick Ship
PGP84	29839	Mild Steel	Powder Coated	No
PGPV65	14683	Mild Steel	Powder Coated	No
PGP65	29779	Mild Steel	Powder Coated	No
PGPV76	14686	Mild Steel	Powder Coated	No
PGP78	29819	Mild Steel	Powder Coated	No
PGPV78	14687	Mild Steel	Powder Coated	No
PGPV89	14694	Mild Steel	Powder Coated	No
PGP89	29879	Mild Steel	Powder Coated	No
PGP79	29829	Mild Steel	Powder Coated	No
PGP104	29848	Mild Steel	Powder Coated	No
PGP105AHF	28929	Mild Steel	Galvanized	No
PGP108AHF	28949	Mild Steel	Galvanized	No
PGP124	29919	Mild Steel	Powder Coated	No
PGP125	29929	Mild Steel	Powder Coated	No
PGP126	29939	Mild Steel	Powder Coated	No
PGP128	29949	Mild Steel	Powder Coated	No
PGP164	29851	Mild Steel	Powder Coated	No
PGP165	29959	Mild Steel	Powder Coated	No
PGP166	29969	Mild Steel	Powder Coated	No
PGP168	29979	Mild Steel	Powder Coated	No

Catalog Number	Article Number	Material	Finish	Quick Ship
PGP185	29989	Mild Steel	Powder Coated	No
PGP186	29999	Mild Steel	Powder Coated	No
PGP188	29852	Mild Steel	Powder Coated	No
PGP45	29847	Mild Steel	Powder Coated	No
PGP46	14274	Mild Steel	Powder Coated	No
PGP64AHF	28809	Mild Steel	Galvanized	No
PGP65AHF	28819	Mild Steel	Galvanized	No
PGP66AHF	28829	Mild Steel	Galvanized	No
PGP68AHF	28839	Mild Steel	Galvanized	No
PGP78AHF	28859	Mild Steel	Galvanized	No
PGP79AHF	28869	Mild Steel	Galvanized	No
PGP88AHF	28909	Mild Steel	Galvanized	No
PGP89AHF	28919	Mild Steel	Galvanized	No
PGPV125	14698	Mild Steel	Powder Coated	No
PGPV126	14701	Mild Steel	Powder Coated	No
PGPV128	14702	Mild Steel	Powder Coated	No
PGPV165	14703	Mild Steel	Powder Coated	No
PGPV166	14704	Mild Steel	Powder Coated	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE