

ProLine Pagoda Exhaust Vents

Pagoda Exhaust Vents can be field-installed on any ProLine or ProLine G2 solid top to provide active enclosure cooling.



FEATURES

Axial fan and finger guard mounted in housing

Drip-protected, raised cover is removable from the inside of the enclosure

115V or 230V versions with lead wires

115V power cord option

Rated UL Type 1; installing this component on an enclosure brings the enclosure rating to UL Type 1

Includes gasket and mounting hardware

SPECIFICATIONS

Thickness: 14ga
Color: Light Gray
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Material	Voltage AC	Hertz	Quick Ship
PPT1	20459	Mild Steel	115V	50/60Hz	No
PPT1C	11095	Mild Steel	115V		No
PPT2	24169	Mild Steel	230V	50/60Hz	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE