


ProLine Pagoda Tops



Pagoda Tops are available to fit on standard frames. Design features a drip-proof raised pagoda vent with a 115-volt integral axial exhaust fan. Double-bay Pagoda Tops have one drip-proof raised pagoda vent opening positioned over one bay that can be oriented for right or left ventilation.

INDUSTRY STANDARDS

This component is rated UL Type 1. Installing this component on an enclosure brings the enclosure rating to UL Type 1.

FEATURES

Bolts secure pagoda top to frame (lifting eyes can be used instead of bolts).

Drip-protected vent

SPECIFICATIONS

Thickness: 14ga
Color: Light Gray
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Material	Frame Type	Quick Ship
PPT66	20259	Mild Steel	Single-Bay	No
PPT68	20269	Mild Steel	Single-Bay	No
PPT85	20319	Mild Steel	Single-Bay	No
PPT88	20339	Mild Steel	Single-Bay	No
PPT64	20239	Mild Steel	Single-Bay	No
PPT86	20329	Mild Steel	Single-Bay	No
PPT105	20359	Mild Steel	Single-Bay	No
PPT106	20369	Mild Steel	Single-Bay	No
PPT108	20379	Mild Steel	Single-Bay	No
PPT84	20309	Mild Steel	Single-Bay	No
PPT65	20249	Mild Steel	Single-Bay	No
PPT76	20279	Mild Steel	Single-Bay	No
PPT78	20289	Mild Steel	Single-Bay	No
PPT89	20349	Mild Steel	Single-Bay	No
PPT79	20299	Mild Steel	Single-Bay	No
PPT126	20409	Mild Steel	Double-Bay	No

Catalog Number	Article Number	Material	Frame Type	Quick Ship
PPT128	20419	Mild Steel	Double-Bay	No
PPT166	20439	Mild Steel	Double-Bay	No
PPT168	20449	Mild Steel	Double-Bay	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE