

ProLine-PC 20-Degree Control Compartment



Reversible design provides 20-degree angled surface for mounting operator controls. Smaller angle maximizes mounting space available. Screw cover on the flat side allows easy access inside compartment. Screw cover has foam-in-place gasketing. Compartment is gasketed around the open rear surface to extend the UL and CSA rating to the control compartment interior. Ground stud and mounting hardware included.

FEATURES

Reversible design

Screw cover on the flat side has foam in place gasket

Ground stud and mounting hardware included.

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
PC20A8	37049	6.89in	31.17in	12.75in	Mild Steel	Powder Coated
PC20A6	37039	6.89in	23.3in	12.75in	Mild Steel	Powder Coated
PC20A6SS	35419	6.89in	23.3in	12.75in	Stainless Steel 304	Brushed
PC20A8SS	35429	6.89in	31.17in	12.75in	Stainless Steel 304	Brushed

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE