

PROLINE-PC Cover for Upper Front



Front Covers for the upper top opening are available in mild steel and stainless steel. Covers are secured with four semi-flush cover screws. Seamless foam-in-place gasket assures water-tight and dust-tight seal. Covers include grounding stud. All mounting hardware is furnished.

FEATURES

Covers available in mild steel and stainless steel

Covers are secured with four semi-flush cover screws

Seamless foam-in-place gasket

All mounting hardware is furnished

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
PCST106PC	98500	78.74in	23.62in	0.69in	Mild Steel	Powder Coated
PCST106PCSS	32059	78.74in	23.62in	0.69in	Stainless Steel 304	Brushed
PCST108PC	98510	78.74in	31.5in	0.69in	Mild Steel	Powder Coated
PCST86PC	98460	62.99in	23.62in	0.69in	Mild Steel	Powder Coated
PCST86PCSS	32049	62.99in	23.62in	0.69in	Stainless Steel 304	Brushed
PCST96PC	98480	70.87in	23.62in	0.69in	Mild Steel	Powder Coated
PCST98PC	98490	70.87in	31.5in	0.69in	Mild Steel	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE