

ProLine S1 Cable Lacing Panel



Vertical cable lacing panel provides tie-down points for small cable bundles. Cable lacing panel features toolless PDU mounting points to double as a full length PDU mounting bracket. Attaches to cabinet frame in the front-to-back depth direction and can be positioned independently of the rack angles. Can be installed with or in place of vertical cable managers. Compatible with cable and power management accessories: Frame Tie Down Brackets (PCMFTD10); D-Ring Cable Managers (ECM3DR10 and ECM6DR10); Cable Spools (PSP00L and P4SP00L); Fiber Management Spool (TOPTKSPL).

FEATURES

Provides tie-down points for small cable bundles

Features toolless PDU mounting points to double as a full length PDU mounting bracket

Attaches to cabinet frame in the front-to-back depth direction

Positions independently of the rack angles

Can be installed with or in place of vertical cable managers

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
PS1CLP45UB	59079	81.41in	4.8in	0.75in	Mild Steel	Powder Coated
PS1CLP48UB	59082	87.32in	4.8in	0.75in	Mild Steel	Powder Coated
PS1CLP48UW	59083	87.32in	4.8in	0.75in	Mild Steel	Powder Coated
PS1CLP45UW	59081	81.41in	4.8in	0.75in	Mild Steel	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE