

ProLine-SY Covers for Lower Front



Solid steel construction. Steel cover is finished in RAL 7035 textured light-gray polyester powder paint (except stainless steel). Seamless foam-in-place gasket assures watertight and dust tight seal. Semi-flush cover screws attach cover to frame. A ground stud is provided.

FEATURES

Seamless foam-in-place gasket assures watertight and dust tight seal

Semi-flush cover screws attach cover to frame. A ground stud is provided

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
PCS88	98720	30.2in	31.17in	0.69in	Mild Steel	Powder Coated
PCS86SS	32109	30.2in	23.31in	0.69in	Stainless Steel 304	Brushed
PCS86	98710	30.2in	23.31in	0.69in	Mild Steel	Powder Coated

ADDITIONAL PRODUCT DETAILS

Covers with openings precut for various manufacturers' HMI devices are available in 600-mm sizes. See Covers with OI Cutouts.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE