


ProLine Vented Plinth Base Cover



Vented Plinth Base Covers install in the front and rear openings of a standard plinth base in place of Solid Covers. Vented covers allow air to circulate into the enclosure. Vented Plinth Base Covers are available in 100-mm and 200-mm heights. These covers include all necessary mounting hardware. A standard plinth base must be ordered in combination with Vented Plinth Base covers to form a Vented Plinth Base. If using a gland plate with the Vented Plinth Base, order a vented gland plate to provide air circulation through the bottom of the enclosure.

FEATURES

Hardware included

Standard plinth base must be ordered in combination with Vented Plinth Base covers to form a Vented Plinth Base

If a gland plate is needed, opt for a vented gland plate for optimum air flow

SPECIFICATIONS

Thickness:	16ga
Color:	Jet Black
Finish:	Powder Coated
Color Code:	RAL 9005

Table 1/1				
Catalog Number	Article Number	Material	Frame Type	Quick Ship
PPBCV2600	13327	Mild Steel	Single-Bay	No
PPBCV1600	13321	Mild Steel	Single-Bay	No
PPBCV1800	13323	Mild Steel	Single-Bay	No
PPBCV2800	13331	Mild Steel	Single-Bay	No
PPBCV11000	13324	Mild Steel	Single-Bay	No
PPBCV21000	13332	Mild Steel	Single-Bay	No
PPBCV1700	13322	Mild Steel	Single-Bay	No
PPBCV2700	13328	Mild Steel	Single-Bay	No
PPBCV11200	13325	Mild Steel	Double-Bay	No
PPBCV11600	13326	Mild Steel	Double-Bay	No
PPBCV21600	13334	Mild Steel	Double-Bay	No

ADDITIONAL PRODUCT DETAILS

200 mm Plinth Bases require two sets of covers.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE