

ProLine Window Doors



Window Doors can be used on the front or rear of ProLine frames to provide viewing of electronic equipment. ProLine Window Doors are designed around a mild steel profile. They have 140-degree hidden hinges and a flush bezel latch that operates a 3-point latching mechanism (doors for 700-mm frames have 2-point latching). Doors have either a smoke-gray tinted polycarbonate or a clear safety glass window; 180-degree hinges are available (order separately).

FEATURES

Install easily on front or rear of enclosure frame; can be hinged on left or right

Have two grounding brackets

Have a .25-in.-thick window that provides maximum protection and viewing area

Have foam-in-place urethane gaskets for door and window to provide optimum sealing

SPECIFICATIONS

Thickness: 14ga

Table 1/1						
Catalog Number	Article Number	Material	Window Size	Window Door Type	Safety Glass	Color
PDW146	90960	Mild Steel	47.94 x 17.55in	Mild Steel, Polycarbonate	52.72 x 23.34in	Light Gray
PDW148	90970	Mild Steel	47.94 x 25.42in	Mild Steel, Polycarbonate	52.72 x 31.22in	Light Gray
PDW166	90980	Mild Steel	55.81 x 17.55in	Mild Steel, Polycarbonate	60.59 x 23.34in	Light Gray
PDW186	91010	Mild Steel	63.69 x 17.55in	Mild Steel, Polycarbonate	68.46 x 23.34in	Light Gray
PDW188	91030	Mild Steel	63.69 x 25.42in	Mild Steel, Polycarbonate	68.46 x 31.22in	Light Gray
PDW206	91040	Mild Steel	71.56 x 17.55in	Mild Steel, Polycarbonate	76.34 x 23.34in	Light Gray
PDW207	91050	Mild Steel	71.56 x 21.48in	Mild Steel, Polycarbonate	76.34 x 27.28in	Light Gray
PDW208	91060	Mild Steel	71.56 x 25.42in	Mild Steel, Polycarbonate	76.34 x 31.22in	Light Gray
PDW226	91070	Mild Steel	79.43 x 17.55in	Mild Steel, Polycarbonate	84.21 x 23.34in	Light Gray
PDW227	91080	Mild Steel	79.43 x 21.48in	Mild Steel, Polycarbonate	84.21 x 27.28in	Light Gray
PDW228	91090	Mild Steel	79.43 x 25.42in	Mild Steel, Polycarbonate	84.21 x 31.22in	Light Gray
PDW76	90940	Mild Steel	20.38 x 17.55in	Mild Steel, Polycarbonate	25.16 x 23.34in	Light Gray
PDW78	90950	Mild Steel	20.38 x 25.42in	Mild Steel, Polycarbonate	25.16 x 31.22in	Light Gray
PDWG146	90800	Mild Steel	47.94 x 17.55in	Mild Steel, Safety Glass	52.72 x 23.34in	Light Gray
PDWG148	90810	Mild Steel	47.94 x 25.42in	Mild Steel, Safety Glass	52.72 x 31.22in	Light Gray
PDWG166	90820	Mild Steel	55.81 x 17.55in	Mild Steel, Safety Glass	60.59 x 23.34in	Light Gray
PDWG168	15179	Mild Steel	55.81 x 25.42in	Mild Steel, Safety Glass	60.59 x 31.22in	Light Gray
PDWG186	15189	Mild Steel	63.69 x 17.55in	Mild Steel, Safety Glass	68.46 x 23.34in	Light Gray

Catalog Number	Article Number	Material	Window Size	Window Door Type	Safety Glass	Color
PDWG188	90870	Mild Steel	63.69 x 25.42in	Mild Steel, Safety Glass	68.46 x 31.22in	Light Gray
PDWG206	90880	Mild Steel	71.56 x 17.55in	Mild Steel, Safety Glass	76.34 x 23.34in	Light Gray
PDWG207	90890	Mild Steel	71.56 x 21.48in	Mild Steel, Safety Glass	76.34 x 27.28in	Light Gray
PDWG208	90900	Mild Steel	71.56 x 25.42in	Mild Steel, Safety Glass	76.34 x 31.22in	Light Gray
PDWG226	90910	Mild Steel	79.43 x 17.55in	Mild Steel, Safety Glass	84.21 x 23.34in	Light Gray
PDWG228	90930	Mild Steel	79.43 x 25.42in	Mild Steel, Safety Glass	84.21 x 31.22in	Light Gray
PDWG76	90780	Mild Steel	20.38 x 17.55in	Mild Steel, Safety Glass	25.16 x 23.34in	Light Gray
PDWG78	90790	Mild Steel	20.38 x 25.42in	Mild Steel, Safety Glass	25.16 x 31.22in	Light Gray

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE