

ProLine Window Doors for Upper Front



Window Doors fit on the upper front of the PC frame and are hinged on the left side. A 2-point latch system is operated by a Small Flush Bezel with tool-to-open insert located on the lower right side of the door. Other inserts and a Flush Swing Handle are also available.

FEATURES

Doors have .25-in.-thick clear safety glass windows

Foam-in-place gaskets for an effective seal

SPECIFICATIONS

Thickness: 14ga

Color: Light Gray Finish: **Powder Coated** Color Code: **RAL 7035**

Table 1/1 **Catalog Number Article Number** Material Window Size **Quick Ship** PDWTL96PC 30869 Mild Steel 17.17 x 17.76in No PDWT96PC 98360 Mild Steel 13.50 x 14.41in No PDWT98PC 98370 Mild Steel 13.50 x 22.28in No PDWT86PC Mild Steel 13.50 x 14.41in 98340 Nο PDWTL86PC 30859 Mild Steel 17.17 x 17.76in No PDWT108PC 98390 Mild Steel 13.50 x 22.28in No PDWT106PC 98380 Mild Steel 13.50 x 14.41in No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE