

Rack-Mount Fan Speed Control



Perfect for offices, classrooms and other noise-sensitive areas, fan Speed Control optimizes airflow in a cabinet or rack, balancing air volume requirements with noise level and power use.

INDUSTRY STANDARDS

UL 508 Listed; File No. E249700

cUL Listed per CSA C22.2 No. 14; File No. E249700

FEATURES

Continuously variable fan speed control knob with minimum speed adjustment

Uses one RU rack space

Steel construction

Two NEMA 5-15R outlets provide power to fan

Six-foot (1.83-m) power cord plugs into standard 120 V 60 Hz outlet

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Max Current	Material
A19FANSC	14073	1.72in	19in	3in	4A	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE