

Raised Side Doors, DNSR



Protects and covers connectors and components mounted to the side of the enclosure to secure and safeguard important connections. A Marshalling plate MM (optional) provides a mounting surface for connectors. Cabling possible from top or bottom with optional cable bars.

FEATURES

Description: A 200 mm wide cover with cable entrances in top and bottom. Supplied with one gland plate and gasket. Hole pattern equals enclosure's frame to mount cable fixing bars.

Material: 2 mm.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP55, Type 12 in combination with HPPG01.

Mounting requirements: Add a separation plate SPD or marshalling plate MM to mount connectors and separate the side compartment.

Pack quantity: 1 piece with mounting accessories.

SPECIFICATIONS

Thickness: 14ga
Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Enclosure Material	Quick Ship
DNSR2006R5	DNSR2006R5	78.74in	23.62in	7.68in	Mild Steel	No
DNSR2005R5	DNSR2005R5	78.74in	19.69in	7.68in	Mild Steel	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE