

Shelf 19-Inch, VSF



This shelf can be adjusted in height and provides further mounting possibilities with a higher loading capacity. It also has ventilation openings to ensure for proper air circulation within the enclosure.

FEATURES

Description: Maximum loading capacity when mounted directly onto the 19" profiles, front and rear. Ventilation openings.

Material: 1.5 mm steel.

Finish: RAL 7035.

Pack quantity: 1 shelf with mounting material.

Maximum load capacity: 1200 N

SPECIFICATIONS

Thickness: 16ga

Color: Light Gray Material: Mild Steel Finish: Powder Coated

Color Code: RAL 7035

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Max Load	Load Rating
VSF1406	VSF1406	0.73in	15.91in	15.91in	270lb	270N
VSF1597	VSF1597	0.73in	23.43in	23.43in	270lb	270N
VSF1470	VSF1470	0.73in	18.43in	18.43in	270lb	270N
VSF1700	VSF1700	0.73in	27.48in	27.48in		

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO TRACHTE HOFFMAN ILSCO SCHROFF