

Side Panels Stainless Steel, SPMS



These side panels will ensure that the ingress protection is maintained, which means that the electrical components will operate without any disturbances and protect personnel from injuries.

FEATURES

Description: Easy one man assembly. Sealed by an extruded, one piece polyurethane gasket and mounted with 8 screws and new patented retainers.

Protection: IP 55, TYPE 12, 13 in combination with MCSS. IP66, TYPE 4X, 12 in combination with MCSS-HP.

Pack quantity: 2 panels with mounting accessories.

Material: 1.5 mm AISI 304 / AISI 316L pre-grained stainless steel.

Finish: 400 pre-grained stainless steel.

SPECIFICATIONS

Thickness: 16ga
Finish: Brushed

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Product Family
SPMS2006-316		77.32in	0.71in	22.13in	Stainless Steel 316	Free-Standing
SPMS1805-316		69.45in	0.71in	18.19in	Stainless Steel 316	Free-Standing
SPMS2006	SPMS2006	77.32in	0.71in	22.13in	Stainless Steel 304	Free-Standing
SPMS1805	SPMS1805	69.45in	0.71in	18.19in	Stainless Steel 304	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE