

SSLP/SSLP3PT Stainless Steel Replacement Door 3Pt Latch 4X



Replacement door for SSLP and SSLP3PT style enclosures. Maintains NEMA Type 4X rating and converts clamp covers to a 3-point latch. Replacement door is ideal for corrosive enclosure installations that require frequent access and the security of a PowerGlide padlocking handle.

INDUSTRY STANDARDS

Maintains NEMA Type 4X rating when properly installed on HOFFMAN SSLP clamp cover or SSLP3PT stainless steel wall-mount enclosures.

FEATURES

Replacement door for SSLP and SSLP3PT enclosures

Seamless foam-in-place gasket

Type 316L stainless steel PowerGlide handle

Internal 3-point latching hardware installed

Data pocket is high-impact thermoplastic

Hinge halves and stainless steel hinge pin

Bonding provision

SPECIFICATIONS

Finish: Brushed #3

Table 1/1						
Catalog Number	Article Number	Material	Thickness	Fits Height	Fits Width	Quick Ship
Z24208SS3PT	14552	Stainless Steel 304	14ga	24in	20in	No
Z24208SS63PT	14562	Stainless Steel 316L	14ga	24in	20in	No
Z24248SS3PT	14553	Stainless Steel 304	14ga	24in	24in	No
Z24248SS63PT	14563	Stainless Steel 316L	14ga	24in	24in	No
Z30248SS3PT	14554	Stainless Steel 304	14ga	30in	24in	No
Z30248SS63PT	14564	Stainless Steel 316L	14ga	30in	24in	No
Z30308SS3PT	14573	Stainless Steel 304	14ga	30in	30in	No
Z30308SS63PT	14574	Stainless Steel 316L	14ga	30in	30in	No
Z36248SS3PT	14555	Stainless Steel 304	14ga	36in	24in	No
Z36248SS63PT	14565	Stainless Steel 316L	14ga	36in	24in	No
Z36308SS3PT	14556	Stainless Steel 304	14ga	36in	30in	No
Z36308SS63PT	14566	Stainless Steel 316L	14ga	36in	30in	No
Z36368SS3PT	14557	Stainless Steel 304	14ga	36in	36in	No
Z36368SS63PT	14567	Stainless Steel 316L	14ga	36in	36in	No
Z48368SS3PT	14558	Stainless Steel 304	14ga	48in	36in	No
Z48368SS63PT	14568	Stainless Steel 316L	14ga	48in	36in	No
Z60368SS3PT	14561	Stainless Steel 304	14ga	60in	36in	No

Catalog Number	Article Number	Material	Thickness	Fits Height	Fits Width	Quick Ship
Z60368SS63PT	14571	Stainless Steel 316L	14ga	60in	36in	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE