

Standard Gland Plates, AF



The gland plate can be easily machined to meet the exact requirements.

FEATURES

Description: Gland plates for the standard gland opening.

Material: 1.4 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 piece.

SPECIFICATIONS

Height:	0.06in
Thickness:	18ga
Color:	Light Gray
Material:	Mild Steel
Finish:	Powder Coated
Color Code:	RAL 7035

Table 1/1

Catalog Number	Article Number	Width	Depth	Gland Plate Type	Gland Plate Opening Width	Gland Plate Opening Depth
AF00SR5	AF00SR5	5.59in	3.46in	0S	4.33in	2.2in
AF01R5	AF01R5	9.53in	5.04in	1	8.27in	3.78in
AF01SR5	AF01SR5	9.53in	3.46in	1S	8.27in	2.2in
AF02R5	AF02R5	13.46in	5.04in	2	12.2in	3.78in
AF02SR5	AF02SR5	13.46in	3.46in	2S	12.2in	2.2in
AF03R5	AF03R5	17.4in	5.04in	3	16.14in	3.78in
AF03SR5	AF03SR5	17.4in	3.46in	3S	16.14in	2.2in
AF04R5	AF04R5	21.34in	5.04in	4	20.08in	3.78in

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE