

# Straight Tube Section Feed-Through Fiberglass



Feed-Through Fiberglass Hinged-Cover, Type 12, 3R  
Straight Tube Sections are used for enclosing wire and cable in wireway runs. The temperature and chemically-resistant fiberglass protects in corrosive or dirty indoor or outdoor applications. Tubes are available in lengths from 12 inch to 120 inch.

## FEATURES

Feed-Through Fiberglass Hinged-Cover, Type 12, 3R Straight Tube Sections are used for enclosing wire and cable in wireway runs

The temperature and chemically-resistant fiberglass protects in corrosive or dirty indoor or outdoor applications

Tubes are available in lengths from 12 inch to 120 inch

## SPECIFICATIONS

**Color Code:** ANSI 61  
**Material:** Fiberglass  
**Color:** Gray  
**Finish:** Smooth Matte

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Depth	Thickness
F44W120STFG	19150	Straight Section	4in	4in	120in	0.12ga
F44W12STFG	19100	Straight Section	4in	4in	12in	0.12ga
F44W24STFG	19110	Straight Section	4in	4in	24in	0.12ga
F44W36STFG	19120	Straight Section	4in	4in	36in	0.12ga
F44W48STFG	19130	Straight Section	4in	4in	48in	0.12ga
F44W60STFG	19140	Straight Section	4in	4in	60in	0.12ga

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**