

Syspend Sanitary HMI Straight Tube

Syspend Sanitary HMI Straight Tube provides structural integrity and acts as conduit for equipment wiring.



CERTIFICATIONS



FEATURES

Type 304 polished stainless steel

Outer diameter of 64 mm (2.50 in.)

Inner diameter of 60 mm (2.37 in.)

2-mm (.06-in.) wall thickness

Assembled Syspend Sanitary HMI Arm System has a max weight load of 90 lb. (40.8 kg)

SPECIFICATIONS

Finish: Polished
Material: Stainless Steel 304

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Thickness	Quick Ship
ST1500SS	19362	59.06in	2.52in	2.52in	0.06in	No
ST250SS	19355	9.84in	2.52in	2.52in	0.06in	No
ST750SS	19357	29.53in	2.52in	2.52in	0.06in	No
ST1250SS	19361	49.21in	2.52in	2.52in	0.06in	No
ST1000SS	19358	39.37in	2.52in	2.52in	0.06in	No
ST500SS	19356	19.69in	2.52in	2.52in	0.06in	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE