

Touch-Safe Heaters, DAH



Protect electronic, mechanical equipment from low temperatures, condensation, and corrosion with this heater, which will maintain stable enclosure temperatures by using natural convection resulting in current circulation of warm air.

INDUSTRY STANDARDS

cURus Component Recognized; File No. E150057

IP 20

CE

FEATURES

Heating element PTC resistor - temperature limiting

Double Insulated Protection

Mounting clip for 35mm DIN rail, EN 60 715

Vertical mount

UL 94 V-0 Plastic Housing

SPECIFICATIONS

Color: Black
Material: Plastic
Finish: Smooth Matte

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Nominal Voltage	Nominal Capacity Watts
DAH101TS	25923	3.9in	1.5in	3in	115V	10W
DAH201TS	25924	3.9in	1.5in	3in	115V	20W
DAH501TS	25925	4.3in	2.4in	3.5in	115V	50W

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE