

CPPSW Tapered Plastic Screw-In Plug with Steel Cap for A2



FEATURES

Designed for use with the A2 coupler families

Designed to keep dirt, water and concrete slurry out of the coupler during the concrete pour

Steel cap provides added protection from damage

Color coded for the appropriate coupler size

SPECIFICATIONS


Material: High Density Polyethylene (HDPE)

Table 1/2							
Catalog Number	Rebar Size, US	Rebar Size, Canada	Diameter 1 (Ø1)	Diameter 2 (Ø2)	Height (H)	Thickness (T)	
EL20CPPSW	#6	20M	1.38"	1.62"	0.59"	0.13"	
EL32CPPSW	#10		2.36"	2.11"	0.71"	0.13"	
EL22CPPSW	#7		1.58"	1.7"	0.71"	0.13"	
EL16CPPSW	#5	15M	1.18"	1.41"	0.59"	0.13"	

CatalogNumber	Rebar Size, US	Rebar Size, Canada	Diameter 1(Ø1)	Diameter 2(Ø2)	Height (H)	Thickness (T)
EL25CPPSW	#8	25M	1.77"	1.82"	0.71"	0.13"
EL12CPPSW	#4	10M	0.98"	1 1/4"	0.59"	0.13"
EL28CPPSW	#9	30M	1.97"	1.95"	0.71"	0.13"

Table 2/2				
Catalog Number	Color			
EL20CPPSW	Yellow			
EL32CPPSW	Yellow			
EL22CPPSW	Blue			
EL16CPPSW	Black			
EL25CPPSW	Red			
EL12CPPSW	Red			
EL28CPPSW	Black			

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE