

# **CPPW Tapered Plastic Screw-In Plug for A2**



### **FEATURES**

Designed for use with the A2 coupler families

Designed to keep dirt, water and concrete slurry out of the coupler during the concrete pour

Color coded for the appropriate coupler size

### **SPECIFICATIONS**


**Material:** High Density Polyethylene (HDPE)

Table 1/2						
Catalog Number	Rebar Size, US	Rebar Size, Canada	Diameter 1 (Ø1)	Diameter 2 (Ø2)	Height (H)	Thickness (T)
EL20CPPW	#6	20M	1.06"	1.62"	0.51"	0.13"
EL32CPPW	#10		1.65"	2.11"	0.63"	0.13"
EL22CPPW	#7		1.3"	1.7"	0.63"	0.13"
EL16CPPW	#5	15M	0.87"	1.41"	0.51"	0.13"
EL25CPPW	#8	25M	1.3"	1.82"	0.63"	0.13"
EL12CPPW	#4	10M	0.67"	1 1/4"	0.51"	0.13"

CatalogNumber	Rebar Size, US	Rebar Size, Canada	Diameter 1(Ø1)	Diameter 2(Ø2)	Height (H)	Thickness (T)
EL28CPPW	#9	30M	1.46"	1.95"	0.63"	0.13"

Table 2/2				
Catalog Number	Color			
EL20CPPW	Yellow			
EL32CPPW	Yellow			
EL22CPPW	Blue			
EL16CPPW	Black			
EL25CPPW	Red			
EL12CPPW	Red			
EL28CPPW	Black			

### **DIAGRAMS**



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

## Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE