

DT14 Swaged Terminator, Plain, 20mm, #6

CATALOG NUMBER

LS20DT14D



The DT14 head area exceeds 10x bar area (net 9x). The system is designed to meet Caltrans Ultimate performance with A706 grade 60 rebar, ASTM A970 Classes A, HA, and B performance with A706 and A615 grade 60 and grade 80 rebar

CERTIFICATIONS



FEATURES

Eliminates reinforcing bar hooks and simplifies bar placement with greater design flexibility

Minimizes embedment lengths and reduces congestion

Simplifies concrete placement

Terminators are permanently secured to the bar and will not loosen or fall off during transportation

Fast installation makes them ideal for high-volume shear ties

Head area exceeds 10x bar area (net 9x)

Meets ASTM® A970 Classes A, HA, and B with grade 60 and grade 80 rebar

PRODUCT ATTRIBUTES

Material: Steel

Finish: Plain

100% U.S. Domestic Content: Yes

Rebar Size, US: #6

Diameter 1 (Ø1): 2.38"

Diameter 2 (Ø2): 1.94"


Length 1 (L1): 2.25"

Length 2 (L2): 0.38"

Unit Weight: 1.7 lb

Designed to Meet: ACI 318;ASTM A970;Caltrans Ultimate (A706 Grade 60)

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE