

nVent LENTON Connect S2 Series Shear Bolt Coupler, Plain



CERTIFICATIONS





FEATURES

Requires no special bar end preparation such as sawing

Installs quickly and easily using simple, off-the-shelf hand tools

Bolt heads shear off when bolt torque is achieved, providing for simple visual inspection

Designed to work as a one-step transition/reducer

Rebar centering pin can be removed to allow the coupler to fully pass onto the reinforcing bar for applications such as closure pours

Complies to ACI 318 Type 1 and Type 2 performance on ASTM A706 grade 60 reinforcing bar

Complies to ACI 318 Type 1 performance on ASTM A615 grade 60 reinforcing bar

Complies to ACI 318-19 Type 2 performance on ASTM A615 grade 60 reinforcing bar

SPECIFICATIONS

Finish: Plain

Material: Steel

100% U.S. Domestic Content: Yes

Table 1/2								
Catalog Number	Rebar Size, US	Rebar Size, Canada	Diameter (Ø)	Length 1 (L1)	Length 2 (L2)	Socket Width (SW)		
LC16S2D	#4, #5	10M, 15M	1.63"	3 1/2"	1.7"	1/2"		
LC20S2D	#6	20M	1.9"	5.1"	2 1/2"	1/2"		
LC22S2D	#7		2"	6.9"	3.4"	1/2"		
LC25S2D	#8	25M	2.38"	8.7"	4.3"	5/8"		
LC28S2D	#9	30M	2.8"	8.7"	4.3"	3/4"		
LC32S2D	#10		3"	11.2"	5.4"	3/4"		
LC36S2D	#11	35M	3.13"	13.7"	6.7"	3/4"		
LC43S2D	#14	45M	3.82"	21"	10.3"	3/4"		

Table 2/2								
Catalog Number	Number of Bolts	Number of Round Bolts	Torque (TQ)	Unit Weight				
LC16S2D	4		85 ft·lbf	1.5 lb				
LC20S2D	6		85 ft·lbf	2.7 lb				
LC22S2D	8		85 ft·lbf	3.9 lb				
LC25S2D	8		193 ft·lbf	7.6 lb				
LC28S2D	6		597 ft·lbf	10.8 lb				
LC32S2D	8		597 ft·lbf	15.2 lb				
LC36S2D	10		597 ft·lbf	19.6 lb				
LC43S2D	14	4	515 ft·lbf	34.95				

ADDITIONAL PRODUCT DETAILS

Bolt length may vary after the bolt heads are sheared off. Bolt heads are not required to be removed as long as the appropriate bolt torque is achieved.

Refer to complete installation instructions provided with the product or available at nVent.com/LENTON prior to commencing installation.

See instructions for installation equipment recommendations.

Round Bolts are located on the outer ends of the coupler, and will shear off at a lower torque than the rest.

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE