

T-Series Vertical Filler Material Kit



T-Series vertical filler material kits contain the following: Filler material, two vertical packings, pouring basin ceramic guide tube and pouring basin crucible ceramic and disk. All filler material kits contain one-time use components that are sized to a specific sleeve, pouring basin and pouring basin crucible combination. Ordering filler material kits simplifies ordering, reduces order errors and helps ensure proper sizing of components.

FEATURES

Simplifies ordering

Used to splice the same diameter bars

All components are for one-time use

SPECIFICATIONS

Table 1/1

Catalog Number	Sleeve	Rebar Size, US	Rebar Size, Canada
RBT121018B	Standard Length	#12	
RBT4101B	Standard Length	#4	10M
RBT5101B	Standard Length	#5	15M
RBT6101B	Standard Length	#6	20M
RBT7101B	Standard Length	#7	
RBT81011B	Extended Length	#8	25M
RBT8101B	Standard Length	#8	25M

Catalog Number	Sleeve	Rebar Size, US	Rebar Size, Canada
RBT91011B	Extended Length	#9	30M
RBT9101B	Standard Length	#9	30M
RBT10911B	Extended Length	#10	
RBT1091B	Standard Length	#10	
RBT111011B	Extended Length	#11	35M
RBT11101B	Standard Length	#11	35M
RBT14101B	Standard Length	#14	45M
RBT1891B	Standard Length	#18	55M

ADDITIONAL PRODUCT DETAILS

Prior to installation, please read and understand all of the detailed instructions and safety notices provided in the nVent LENTON Cadweld Rebar Splicing System instruction manual.

Filler material kits are a component in splice kits. Care should be taken to avoid duplication of orders.

Components can also be purchased separately: (1) Filler Material, (2) Vertical Top Packing, (3) Vertical Bottom Packing, (4) Pouring Basin Ceramic Guide Tube, and (5) Crucible Ceramic and Disk.

Filler Material Kit Components				
Filler Material Kit	Filler Material	Packing (2 Required)	Pouring Basin Ceramic Insert and Disk	Pouring Basin Ceramic Guide Tube
RBT4101B	RBF40	RBS354710 RBS354710	RBS5037	RBS5039
RBT5101B	RBF40	RBS354710 RBS35475	RBS5037	RBS5038
RBT6101B	RBF50	RBS35473.5 RBS35477	RBS5037	RBS5038
RBT7101B	RBF50	RBS35474 RBS35478	RBS5037	RBS5038
RBT81011B	RBF70	RBS354710 RBS35475	RBS5037	RBS5038
RBT8101B	RBF55	RBS354710 RBS35475	RBS5037	RBS5038
RBT91011B	RBF90	RBS354711 RBS35475.5	RBS5037	RBS5038
RBT9101B	RBF80	RBS354711 RBS35475.5	RBS5037	RBS5038
RBT10911B	RBF105	RBS354712 RBS35476	RBS5037	RBS5038
RBT1091B	RBF90	RBS354712 RBS35476	RBS5037	RBS5038
RBT111011B	RBF125	RBS354712 RBS35476	RBS5037	RBS5038
RBT11101B	RBF105	RBS354712 RBS35476	RBS5037	RBS5038
RBT121018B	RBF180	RBS354715 RBS35477	RBS5037	RBS5038
RBT14101B	RBF195	RBS354715 RBS35477	RBS5037	RBS5039
RBT1891B	RBF270	RBS354720 RBS35479	RBS5037	RBS5039

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE