


MultipacPRO 19" Chassis, Aluminum, Plain Top and Base, 4 U, 340 mm

Power Utilities

CATALOG NUMBER

20860-612



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have plain top and bottom cover.

CERTIFICATIONS



FEATURES

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

PRODUCT ATTRIBUTES

Product Type: Subrack/Chassis
Product Family: MultipacPRO
Type: Solid
Rack Height: 4 U
EMC Shielding: No (Retrofittable)
Mounting: Rack
Complies With: IEC 60297-3-100

ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE