

Varistar CP Seismic Base/Plinth, 103H 800W 600D

Power Utilities

CATALOG NUMBER

21630-115

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

FEATURES

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

PRODUCT ATTRIBUTES

Product Type: Cabinet/Rack Base

Product Family: Varistar CP

Type: Base Plinth

Material: Steel

Color: Black Grey

Color Code: RAL 7021

Complies With: IEC 61587-1; IEC 61587-2

Works With: Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE