

Front Panel, Front Shielded, Side Hinged

Power Utilities

Front panel with textile EMC gasket, side hinged assembly.



CERTIFICATIONS



FEATURES

Front panel with textile EMC gasket

Enables mounting onto the horizontal rails

Suitable for sub racks and cases

Hinges can be fitted on left or right

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Package Quantity	Mounting	EMC Gasket Type	Front Finish	Rear Finish
20848-617	6 U	1	Hinged, Side	Textile	Anodized	Conductive
20848-611	3 U	1	Hinged, Side	Textile	Anodized	Conductive

Table 2/2

Catalog Number	Treated Edges	EMC Shielding	Material	Product Type	Rack Width	Type
20848-617	No	No (Retrofittable)	Aluminum	Front Panel	84 HP	Front Panel without Handle
20848-611	No	No (Retrofittable)	Aluminum	Front Panel	84 HP	Front Panel without Handle

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE