

MultipacPRO 19" Chassis, Aluminum, Perforated Top and Base

Power Utilities



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have perforated top and bottom cover for better air flow and heat dissipation.

CERTIFICATIONS



FEATURES

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

SPECIFICATIONS

Table 1/2						
Catalog Number	Rack Height	Mounting	Complies With	EMC Shielding	Product Family	Product Type
20860-621	1 U	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)	MultipacPRO	Subrack/Chassis
20860-622	1 U	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)	MultipacPRO	Subrack/Chassis
20860-624	2 U	Rack	IEC 60297-3-100	No (Retrofittable)	MultipacPRO	Subrack/Chassis
20860-625	2 U	Rack	IEC 60297-3-100	No (Retrofittable)	MultipacPRO	Subrack/Chassis
20860-626	2 U	Rack	IEC 60297-3-100	No (Retrofittable)	MultipacPRO	Subrack/Chassis
20860-627	3 U	Rack	IEC 60297-3-100	No (Retrofittable)	MultipacPRO	Subrack/Chassis
20860-628	3 U	Rack	IEC 60297-3-100	No (Retrofittable)	MultipacPRO	Subrack/Chassis
20860-629	3 U	Rack	IEC 60297-3-100	No (Retrofittable)	MultipacPRO	Subrack/Chassis
20860-630	3 U	Rack	IEC 60297-3-100	No (Retrofittable)	MultipacPRO	Subrack/Chassis
20860-632	4 U	Rack	IEC 60297-3-100	No (Retrofittable)	MultipacPRO	Subrack/Chassis
20860-633	4 U	Rack	IEC 60297-3-100	No (Retrofittable)	MultipacPRO	Subrack/Chassis
20860-634	4 U	Rack	IEC 60297-3-100	No (Retrofittable)	MultipacPRO	Subrack/Chassis
20860-635	5 U	Rack	IEC 60297-3-100	No (Retrofittable)	MultipacPRO	Subrack/Chassis

Table 2/2		
Catalog Number	Type	Certifications
20860-621	Perforated	RoHS
20860-622	Perforated	RoHS
20860-624	Perforated	

Catalog Number	Type	Certifications
20860-625	Perforated	RoHS
20860-626	Perforated	RoHS
20860-627	Perforated	RoHS
20860-628	Perforated	RoHS
20860-629	Perforated	RoHS
20860-630	Perforated	
20860-632	Perforated	RoHS
20860-633	Perforated	RoHS
20860-634	Perforated	RoHS
20860-635	Perforated	RoHS

ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE