



We connect and protect

# RackPower Basic PDU, RB0xxx, 120/208 VAC, 3-phase

## Power Utilities

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 / C19 Combo outlets.

### FEATURES

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 100-120/200-240VAC, 3-phase WYE

Connecting cable 6", with NEMA L21 connector

C13 and C13/C19 Combo outlets

1RU aluminum profile

Adjustable Toolless Mounting

### SPECIFICATIONS

Table 1/1

| Catalog Number | Product Type | Socket Type          | Color | Voltage AC |
|----------------|--------------|----------------------|-------|------------|
| RB0851         | Socket Strip | IEC C13, IEC C13/C19 | Black | 208 V      |

### ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**