

Varistar CP Double Steel Door, Perforated, 3-Point Locking

Power Utilities

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

FEATURES

Double perforated steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Color	Color Code	Complies With	Locking Type	Product Type
21630-020	42 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-021	47 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-022	52 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-027	42 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-028	47 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-029	52 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-448	24 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door

CatalogNumber	Rack Height	Color	Color Code	Complies With	Locking Type	Product Type
21630-449	24 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-450	29 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-451	29 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-452	33 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-453	33 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-454	38 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-455	38 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door

Table 2/2

Catalog Number	Protection Rating	Type	Works With
21630-020	IP20	Steel Double Door, Perforated	Varistar CP
21630-021	IP20	Steel Double Door, Perforated	Varistar CP
21630-022	IP20	Steel Double Door, Perforated	Varistar CP
21630-027	IP20	Steel Double Door, Perforated	Varistar CP
21630-028	IP20	Steel Double Door, Perforated	Varistar CP
21630-029	IP20	Steel Double Door, Perforated	Varistar CP
21630-448	IP20	Steel Double Door, Perforated	Varistar CP
21630-449	IP20	Steel Double Door, Perforated	Varistar CP
21630-450	IP20	Steel Double Door, Perforated	Varistar CP
21630-451	IP20	Steel Double Door, Perforated	Varistar CP

Catalog Number	Protection Rating	Type	Works With
21630-452	IP20	Steel Double Door, Perforated	Varistar CP
21630-453	IP20	Steel Double Door, Perforated	Varistar CP
21630-454	IP20	Steel Double Door, Perforated	Varistar CP
21630-455	IP20	Steel Double Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE