

Varistar CP Double Steel Door, Plain, 3-Point Locking

Power Utilities

Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

FEATURES

Double steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Color	Color Code	Complies With	Locking Type	Product Type
21630-086	42 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-087	47 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-088	52 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-089	42 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-090	47 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-091	52 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-440	24 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door

CatalogNumber	Rack Height	Color	Color Code	Complies With	Locking Type	Product Type
21630-441	24 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-442	29 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-443	29 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-444	33 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-445	33 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-446	38 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door
21630-447	38 U	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3	3-Point Locking	Cabinet Door

Table 2/2

Catalog Number	Protection Rating	Type	Works With
21630-086	IP20	Steel Double Door	Varistar CP
21630-087	IP20	Steel Double Door	Varistar CP
21630-088	IP20	Steel Double Door	Varistar CP
21630-089	IP20	Steel Double Door	Varistar CP
21630-090	IP20	Steel Double Door	Varistar CP
21630-091	IP20	Steel Double Door	Varistar CP
21630-440	IP20	Steel Double Door	Varistar CP
21630-441	IP20	Steel Double Door	Varistar CP
21630-442	IP20	Steel Double Door	Varistar CP
21630-443	IP20	Steel Double Door	Varistar CP

Catalog Number	Protection Rating	Type	Works With
21630-444	IP20	Steel Double Door	Varistar CP
21630-445	IP20	Steel Double Door	Varistar CP
21630-446	IP20	Steel Double Door	Varistar CP
21630-447	IP20	Steel Double Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE